## PROGRESSIVE GROUP AUSTRALIA & NEW ZEALAND AUSTRALIA & NEW ZEALAND



**SYSTEM** 

The RONA™ SECUJET® was especially designed for small and medium producers or for the processing of smaller batches within larger operations. Main applications are filtration of beer, wine, other beverages as well as other liquids with strict hygienic requirements.

The RONA™ SECUJET® is a compact precoat candle filter, completely skidmounted on wheels. It incorporates the patented RONA™ STABOX® filter candle technology. It can be operated with Diatomaceous Earth or other Filter Aids to remove yeast cells, bacteria, and other unwanted small particles.

User friendly, easy to operate

- High flow rates
- Low capital investment costs
- High pressure stability
- Very low maintenance no moving parts, no internal seals
- Easy cleaning no need to open filter for D.E. discharge and rinsing
- Very low product loss because of residual filter elements
- Integrated frequency controlled process pump
- Filter vessel is fully certified according to DGR/PED

The RONATM STABOX® candles with  $70\mu$  slots ensure equal distribution of filter aids and avoid



Туре	Secujet 60 / 445 General Version	Secujet 60 / 445 BF Special Version for Beer Filtration	Secujet 60 / 320 General version
Pressure	0 – 6 bar	0 – 6 bar	0 – 6 bar
Operating Temperature	0 – 100° C	0 – 100° C	0 – 100° C
Max. flow rate	20 hl / m² / h	5 hl / m² / h	20 hl / m² / h
Min. flow rate	2,5 hl / m² / h	2.5 hl / m² / h	2.5 hl / m² / h
Slurry volume	1581	1581	1101
Pump speed	41 – 170 hl / h	27 – 110 hl / h	27 – 110 hl / h
Filter Area	8.4 m <sup>2</sup>	8.4 m²	5.6 m <sup>2</sup>
Volume of dosing tank	130	130	1301
Speed of stirer in dosing tank	86 – 91 U / min	38 U / min	95 – 114 U / min
Performance of dosing pump	0.75 kW	0.75 kW	0.75 kW
Dosing flow rate	25 – 380 hl / h	16 – 160 hl / h	16 – 160 hl / h
Performance of process pump	7.5 kW	5.5 kW	5.5 kW
Weight of base plate with candles	156 kg	156 kg	135 kg
Weight of hood	94 kg	94 kg	74 kg
Weight of complete unit (empty)	606 kg	606 kg	566 kg
Weight of complete unit (operating)	1250 kg	1250 kg	1125 kg

breakthroughs. Base plate with candles. The short candles for residual filtration allow to press out the filter with air/gas in order to minimize product losses.